



burkert









A rotork Brand

Fine Controls have been supplying process controls & instrumentation equipment since 1994, & now serves an ever expanding customer base, both in the UK & globally.

We offer a full range of valve & instrumentation products & services, with our product rangerepresenting leading technologies & brands:

Flow: Flow Meters & Transmitters, Flow Switches, Flow Control Valves & Batch Control Systems

Temperature: Temperature Probes & Thermowells, Temperature ransmitters, Temperature Regulators & Temperature Displays

Level: Level Transmitters & Switches

Pressure: Pressure Gauges & Transmitters, Precision & High Pressure Regulators & I-P Converters, Volume boosters.

Precision Pneumatics: Pressure Regulators, I-P Converters, Volume Boosters, Vacuum Regulators

Valves: Solenoid & Pneumatic Valves, Control Valves & Positioners, Actuated Ball, Globe or Diaphragm Valves & Isolation Valves

Services: Repair, Calibration, Panel Build, System Design & Commissioning



A rotorik Brand



Honeywell



Baumer Group









Fine Controls (UK) LTD, Bassendale Road, Croft Business Park, Bromborough, Wirral, CH62 3QL UK Tel: 0151 343 9966 Email: sales@finecontrols.com

Model 30 Midget Precision Regulator

Model 30



The Model 30 is designed for applications that require high capacity and accurate process control in a small package. A poppet valve which is balanced by utilizing a convoluted diaphragm, insures a constant output pressure even during wide supply pressure variations. Stability of regulated pressure is maintained under varying flow conditions through the use of an aspirator tube which adjusts the air supply in accordance with the flow velocity.

Features

- Control sensitivity of 1/4" water column variation allows use in precision applications.
- A compensating diaphragm lets the regulator remain unaffected by supply pressure changes.
- Flow of up to 40 SCFM with 100 psig supply allows use in applications with high flow requirements.
- An aspirator tube compensates downstream pressure droop under flow conditions.
- A separate Control Chamber isolates the diaphragm from the main flow to eliminate hunting and buzzing.
- Unit construction lets you service the Model 30 without removing it from the line.
- Canadian Registration Number (CRN) Certification for all territories and provinces.

Operating Principles

The Model 30 Regulator uses the force balance principal to control the movement of the valve assembly which in turn controls the output pressure. When the regulator is adjusted for a specific set point, the downward force of the Positive Bias Spring causes the Diaphragm Assembly to move downward. The Supply Valve opens and allows air to pass to the Outlet Port. As the set point is reached, the downward force exerted by the Positive Bias spring is balanced by the upward force of the downstream pressure acting on the bottom of the Diaphragm Assembly. The resultant force moves the supply Valve upward to reduce the flow of air to the Outlet Port.

Outlet pressure is maintained as a result of balance between forces acting on the top and bottom of the Diaphragm Assembly.



Technical Information



Specifications

Supply Pressure

250 psig, [17.0 BAR], (1700 kPa) Maximum

Flow Capacity

40 SCFM (68 m³/HR) @ 100 psig, [7.0 BAR], (700 kPa) supply and 20 psig, [1.5 BAR], (150 kPa) setpoint

Exhaust Capacity

2.0 SCFM (3.4 m³/HR) where downstream pressure is 5 psig, [.35 BAR], (35 kPa) above 20 psig, [1.5 BAR], (150 kPa) setpoint

Supply Pressure Effect

Less than 0.2 psig, [.014 BAR], (.14 kPa) for 100 psig, [7.0 BAR], (700 kPa) change in supply pressure

Sensitivity

1/4" (.63cm) Water Column

Ambient Temperature

-40°F to +200°F, (-40°C to 93.3°C)

Hazardous Locations

Acceptable for use in Zones 1 and 2 for gas atmosphere: Groups IIA and IIB and Zones 21 and 22 for dust atmospheres

Materials of Construction

| Body and Housing Al | uminum |
|-----------------------|--------|
| Diaphragms Nitrile on | Dacron |
| Trim | Brass |

Model 30 Midget Precision Regulator

Model

30

Catalog Information

| Catalog Number | | 302 | | |
|----------------|----------|----------|---|---|
| Pressure R | lange | | | |
| psig | [BAR] | (kPa) | | |
| 0-2 | [0-0.1] | (0-15) | 1 | |
| 0-10 | [0-0.7] | (0-70) | 2 | |
| 0.5-30 | [0.03-2] | (3-200) | 3 | |
| 1-60 | [0.1-4] | (10-400) | 4 | |
| 2-100 | [0.1-7] | (15-700) | 5 | |
| Dino Sizo | | | | |
| Pipe Size | | | | |
| 1/4" NPT . | | | 2 | 2 |
| 3/8" NPT . | | | | 3 |

| Options |
|-------------------------------|
| Silicone Elastomers 1 |
| Low Bleed |
| BSPP (Parallel) ² |
| Fluorocarbon *Elastomers |
| Low Flow |
| Non-Relieving |
| Plunger Operated ³ |
| Screwdriver Adjust |
| Tamper Proof |
| BSPT (Tapered) |
| |

| | Α | В | Н | J | L | Ν | R | S | Т | U |
|---|---|---|---|---|---|---|---|---|---|---|
| Α | - | Y | Y | Ν | Y | Y | Y | Y | Y | Υ |
| В | Y | - | Y | Y | Ν | Ν | Ν | Y | Y | Y |
| Η | Y | Y | - | Y | Y | Y | Y | Y | Y | Ν |
| J | Ν | Y | Y | - | Y | Y | Y | Y | Y | Υ |
| L | Y | Ν | Y | Y | - | Ν | Y | Y | Y | Y |
| Ν | Y | Ν | Υ | Υ | Ν | - | Y | Y | Y | Υ |
| R | Y | Y | Y | Ν | Y | Y | - | Y | Ν | Y |
| S | Y | Y | Υ | Y | Y | Y | Ν | - | Ν | Υ |
| Т | Y | Y | Υ | Y | Y | Y | Ν | Ν | - | Υ |
| U | Y | Y | Ν | Y | Y | Y | Y | Y | Y | - |

¹ Maximum Supply Pressure - 75 psig, [5.0 BAR], (500 kPa)

² BSPP Threads in Inlet & Outlet Ports Only. Others BSPT.

³ Refer to Table 1 for Push Rod Travel and Thrust

* Viton

| Table 1. Plunger Operated Regulator Parameters | | | | | |
|--|-----------------------------|-----------------------------|--|--|--|
| Range | Push Rod Travel (inches) | Push Rod Thrust (pounds) | | | |
| 0-2 psig | .244 ± 10% | 3.2 ± 10% | | | |
| 0-10 psig | .344 ± 10% | 15.7 ± 10% | | | |
| 0-30 psig | .333 ± 10% | 47.0 ± 10% | | | |
| 0-60 psig | .395 ± 10% | 94.0 ± 10% | | | |
| 0-100 psig | .354 ± 10% | 157.0 ± 10% | | | |

Installation

For installations instructions, refer to the Fairchild Model 30 Midget Precision Regulator Instruction, Operation and Maintenance Instructions, IS-10000030.

