



burkert









A rotork Brand

Fine Controls have been supplying process controls & instrumentation equipment since 1994, & now serves an ever expanding customer base, both in the UK & globally.

We offer a full range of valve & instrumentation products & services, with our product rangerepresenting leading technologies & brands:

Flow: Flow Meters & Transmitters, Flow Switches, Flow Control Valves & Batch Control Systems

Temperature: Temperature Probes & Thermowells, Temperature ransmitters, Temperature Regulators & Temperature Displays

Level: Level Transmitters & Switches

Pressure: Pressure Gauges & Transmitters, Precision & High Pressure Regulators & I-P Converters, Volume boosters.

Precision Pneumatics: Pressure Regulators, I-P Converters, Volume Boosters, Vacuum Regulators

Valves: Solenoid & Pneumatic Valves, Control Valves & Positioners, Actuated Ball, Globe or Diaphragm Valves & Isolation Valves

Services: Repair, Calibration, Panel Build, System Design & Commissioning



A rotorik Brand



Honeywell



Baumer Group









Fine Controls (UK) LTD, Bassendale Road, Croft Business Park, Bromborough, Wirral, CH62 3QL UK Tel: 0151 343 9966 Email: sales@finecontrols.com





Volume boosters are normally used to reproduce pneumatic signals in 1:1 ratio whenever input isolation or increased flow capacity is required. These high capacity Volume Boosters, with a fixed minimum deadband, are designed to substantially improve the stroking speeds of large actuators.

Actuators retain their normal slow and stable responses as long as their signal fluctuations remain within the deadband limits that are determined by adjustment of the equalizing / bypass valve within the Booster.

Design Features :

- · Built-in adjustable by-pass valve with fine control
- · Capable of using high pressure plant air suppliers
- \cdot Various sizes available to suit wide range of actuator sizes
- · Robust parts for trouble free service
- $\cdot\,$ Main internal air supply valve with soft seat insert
- Highly corrosion resistant with external stainless steel retaining screws and internal wear parts
- · Stainless Steel and Aluminium construction available



Model 1000



Model 1000 - Overall Dimensions

Performance Features :

- $\cdot\,$ Low air consumption, soft seat insert gives tight shut-off
- · Quick response with increased actuator stroking speeds
- $\cdot\,$ Maintains correct actuator positioning at high stroking speeds
- · Adjustable bypass valve provides good operational sensitivity
- $\cdot\,$ High stability which allows normal slow actuator response to the
- slow signal changes produced by usual process control variations

Associated Benefits :

- · Rigorously proven on-site performance
- · Minimal inspection and maintenance costs
- $\cdot\,$ Low cost of ownership
- · Assured product quality



Severe & Hazardous Area Experts

Application :

The Volume boosters are normally used to reproduce pneumatic signals in 1:1 ratio whenever input isolation or increased flow capacity is required. These units can substantially increase the stroking speeds of large actuators while maintaining the normal stable respones, providing the signal fluctuations remain within the levels determined by the deadband limits which are adjustabe, via an equalising/bypass valve fitted on both sizes of booster.



Operation :

In operation during normally steady state process conditions, with small variations in the controller or positioner signals, the signal input flow to the booster will pass through the integral equalizing/bypass valve and into the actuator. Both booster ports remain tightly shut with the soft seating inserts preventing unnecessary air consumption.

With large or faster variations in signal flow the equalizing/bypass valve setting causes them to be registered sooner on the booster inlet than on its outlet which is connected to the actuator. When the differential pressure obtained exceeds the deadband value of the booster, set by the adjustable equalizing/bypass valve, the diaphragm assembly will move as to open one or other booster port and allow rapid change of pressure within the actuator. When the pressure balance is restored, with the positioner or controller sensing that the corrective action is completed, the booster closes and allows the system to resume normal operation with the actuator being fed via the equalizing/bypass valve flow.



Specifications :

Supply / Output connection: ¼", ½" or ¾" NPT (F) Signal Connection: ¼" NPT (F) Supply Pressure: Up to 150 psig (10.3 bar) Pressure Ratio: 1 : 1 Ambient Temperature: -40°C to + 70°C (-40°F + 160°F) Deadband Width: 1psig (0.7 bar) or 5% of output span, whichever is greater Model 3000 - Dimensions

Methane (Natural Gas) Flow Capacity: Series 1000 Cv (In-Out) - 0.5 CV (Out - exhaust) - 0.5 Series 3000 Cv (In-Out) - 3.5 CV (Out - exhaust) - 2.5

Operating Supply Gases: Air, Nitrogen,







Item	Description	Materials
1	Bottom Nut	Brass*
2	Body Gasket	Neoprene
3	Spring	Stainless Steel
4	Plug	Stainless Steel
5	Soft Seat	Teflon
6	Body	Aluminium
7	Area Plate Assembly	Aluminium
8	Soft Seat	Teflon
9	Diaphragm	Neoprene
10	Socket Head Screw	Stainless Steel
11	Top Cover	Aluminium
12	O Ring	Nitrile
13	Adjusting Screw	Stainless Steel
14	Spacer	Aluminium

*Stainless Steel construction can be supplied



Sectional View Model 3000

*Stainless Steel construction can be supplied

ACCURACY AND COMPLETENESS OF INFORMATION

All information in this literature regarding products and services provided by Midland-ACS is subject to change without prior notice. Reasonable efforts are taken to ensure the accuracy and integrity of all information provided here, but Midland-ACS is not responsible for misprints, out-of-date information, or errors. Midland-ACS makes no warranty, express or implied, or assumes any legal liability or responsibility for the accuracy or completeness of any information contained in this literature

United Kingdom Headquarters Midland-ACS Patrick Gregory Road,

Wolverhampton, WV11 3DZ United Kingdom Tel: +44 (0)1902 305678 Fax: +44 (0)1902 305676 Email: midland-acs@itt.com North American Headquarters Midland-ACS North America P.O. Box 422, Ontario L3M 4H8, Canada Tel: (905) 309-1834 Fax: (905) 309-1835 Email: rjthake@aol.com

Sectional View Model 1000

Item	Description	Materials
1	Body	Aluminium*
2	Gasket O Ring	Nitrile
3	Blind Nut	Brass*
4	Spring	304 St. Steel
5	Plug	St.Steel/Nitrile
6	O Ring	Nitrile
7	Seat Ring	Brass
8	Lock Nut	Stainless Steel
9	Exhaust Seat	Aluminium*
10	Diaphragm Plate	Aluminium*
11	Diaphragm	Nitrile/Nylon
12	Spacer	Aluminium*
13	Spring Housing	Stainless Steel
14	Spring	304 St. Steel
15	Cover	Aluminium*
16	O Ring	Nitrile
17	Lock Nut	Stainless Steel
18	Adjusting Screw	Stainless Steel
19	Backing Plate	Aluminium*
20	Cover Screw	Stainless Steel